

Features

- Excellent molten splash and flame resistance
- Continuous working temperature of 200°C (500°F)
- Superb abrasion and moisture resistance
- Very flexible and available in different colours
- Provides protection from ozone and UV
- Insulates against energy loss in piping and hosing
- Max short time exposure 1650°C (3000°F)
- Available in Red, Black, Yellow, Blue, White and Silver

RS PRO Fire Sleeve White 1m

RS Stock No.: 0731297



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS Pro Fire Sleeve is designed to protect hoses, wires and cables from the hazards of high heat and occasional flame. Made of braided fiberglass yarns in a flexible substrate, it is then coated with high grade silicone rubber. The thick formulation of silicone rubber sheds molten splash, slag, welding splatter, electrical or grinding sparks and contamination. RS Pro Fire Sleeve's key applications are protecting hydraulic hoses, cables and wiring. Used in metallurgy, steel mills, glass works, marine industry and petrochemical industry.

General Specifications

Part Number	Ordering Size (mm)
0730396	4
0730397	6
0730398	8
0730399	10
0730400	12
0730401	14
0731278	16
0731279	19
0731280	22
0731281	25
0731282	28
0731283	32
0731284	35
0731285	38
0731286	41
0731336	44
0731288	51
0731289	57
0731290	63
0731291	70
0731292	76
0731294	83
0731295	89
0731296	95
0731297	102
0733705	114
0733706	127
0733707	140
0733708	152
0733709	168
0733710	180
0733711	203

Approvals

Declarations	Compiles with EN 45545-2 Tested to ISO 11925-2
Standards Met	Meets requirement for IEC 60695-11-10 Classified as HB an V0 Meets requirements for UL94 V0,V1,V2