

Product Information

Page 1 of 2


EPIC® MC Module: High Voltage 3pole Valid: 01.12.2008

Product Description

Mixed assembly guarantees a high flexibility.









Application range

- · Plant engineering and construction
- Control technology

Benefits

• Mixed assembly guarantees a high flexibility.

Cross-References

Suitable housing:

EPIC® MCR 6, EPIC® MCR 10, EPIC® MCR 16, EPIC® MCR 24

Suitable contacts:

EPIC® MC 3.6 machined contacts

Accessories

EPIC® MC Module removal tool, EPIC® MCR 6, EPIC® MCR 10, EPIC® MCR 16, EPIC® MCR 24



EPIC® MC Module: High Voltage 3pole Valid: 01.12.2008

Technical Data

Rated voltage in V

1000 V

Rated current in A

50 A

Contact resistance

< 2 m?
Contacts

Copper alloy, hard silver plated

Number of contacts

3

Termination methods

Crimp termination: 1.5 - 10.0 mm²

Cycle of mechanical operation

100

Range of temperature

-40°C - +100°C, temporary up to +125°C

Pollution degree

3

Article List

Part number	Part	Version	Contacts	Pieces / PU
Module: High Voltage 3 pole				
10399800	MCS 3 CM-HV	male	3	10
10399900	MCB 3 CM-HV	female	3	10