



Product Datasheet

ENGLISH

Stock No: 192-4383

Video Borescope



1. General Specifications

The Video Borescope is an extendable video camera used to view inaccessible areas. It features a durable camera snake with an adjustable intensity LED worklight, a 2.4" LCD screen, auto power off, and screen mirroring.

- **Dimensions:** 6.53" x 2.84" x 1.55" (16.59 x 7.22 x 3.95 cm)
- **Weight (Main Unit):** 8.08 oz. (229.3 grams)
- **Weight (Gooseneck Camera):** 1.73 oz. (49.0 grams)
- **Operating Altitude:** 2000 meters
- **Operating Temperature:** 0°C /32°F to 50°C / 122°F
- **Storage Temperature:** -20°C/ -4°F to 60°C / 140°F
- **Relative Humidity:** 85%
- **Environmental Protection (Gooseneck Camera):** IP67 (dust proof, water immersible up to 1 meter for up to 30 minutes)
- **Certifications:** CE, WEEE
- **Screen Resolution:** 480 x 234px
- **Color Depth:** 24 bits
- **Fixed Focus Distance:** 1.97"~5.90" (5~15cm)
- **Camera Diameter:** 0.67" (17mm)
- **Gooseneck Length:** 3.28' (1m)
- **Battery Life (Typical):** 3 hours continuous operation (LEDs off)