

# Rear panel & door, PrismaSeT G, W 300mm, H 450mm (7M), IP55for extension duct

LVS08342

EAN Code: 3606481884756

## Main

Range	PrismaSeT	
Range of product	PrismaSeT G	
Product or component type	Door Rear panel	
Device application	Low voltage electrical distribution	
Enclosure type	Functional enclosure delivered in kit form	
Provided equipment	1 x door for enclosure	
Additional information	Can be combined side by side and one on top of another	
type of front plate	Without	
Number of vertical modules [50 mm]	7	
Number of 18 mm modules per row	10	

## Complementary

[Ui] rated insulation voltage	1000 V	
[In] rated current	630 A at 40 °C conforming to IEC 61439-2	
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder	
Surface finish	Smooth Matt	
Colour	White (RAL 9001)	
Width	300 mm	
Height	450 mm	
Depth	260 mm	
Net weight	8.82 kg	
Quantity per set	Set of 1	

## **Environment**

IP degree of protection	IP55 with door	
IK degree of protection	IK10 with door conforming to EN/IEC 62262	
Mechanical robustness	chanical robustness Seismic tests - 2.5G conforming to IEC 60068-2-57	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	11 cm
Package 1 Width	36 cm
Package 1 Length	44 cm
Package 1 Weight	8.595 kg
Unit Type of Package 2	P12
Number of Units in Package 2	5
Package 2 Height	37 cm
Package 2 Width	80 cm
Package 2 Length	120 cm
Package 2 Weight	55 kg

# **Logistical informations**

Country of origin

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability

Environmental Disclosure

Product Environmental Profile

#### **Use Better**


Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

## **Technical Illustration**

#### **Dimensions**



- All dimensions are approximate and are ir Also see technical documentation.