FO patch cable - FOC-ST:PA-ST:PA-OM2:D01/2 - 1115557

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Multi-mode OM2 duplex jumper, ST-ST, UPC polishing, length 2 m

Your advantages

- Glass fiber optical, 8-shaped FO cable jumper
- Indoor use, suitable for fiber optics distribution and termination devices
- Made of halogen-free flame retardant material, RoHS compliant

RoHS IP20

Key Commercial Data

Packing unit	1 pc
GTIN	4 063151 039660
GTIN	4063151039660
Weight per Piece (excluding packing)	37.700 g
Custom tariff number	85447000
Country of origin	China
Sales Key	ABNACF

Technical data

Dimensions

Length of cable	2.00 m

Ambient conditions

Ambient temperature (assembly)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 60 °C
Ambient temperature (operation)	-20 °C ... 60 °C

General

Number of positions	2
Standards/regulations	IEC 61300-3-4 RL: IEC 61300-3-6

FO patch cable - FOC-ST:PA-ST:PA-OM2:D01/2 - 1115557

Technical data

General

Insertion/withdrawal cycles	≥ 500
Transmission characteristics (category)	OM2
Halogen-free	complying with IEC 60754-1/2
Resistance to oil	Not resistant to oil, gasoline, acids, and lyes
Flame resistance	yes

Material

Flammability rating according to UL 94	V0

Cable

Cable abbreviation	I-V(ZN)H
Cable structure	Figure 8 cable
External cable diameter	2.00 mm
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	30 mm
Cable weight	5.30 kg/km
External sheath, color	orange
Outer sheath, material	LSZH
Standards/specifications	IEC 61300-3-4 RL: IEC 61300-3-6
Transmission speed	1 bps
Flame resistance	yes
Halogen-free	complying with IEC 60754-1/2
Resistance to oil	Not resistant to oil, gasoline, acids, and lyes
Concentration of fumes	in accordance with IEC 61034

Standards and Regulations

Concentration of fumes	in accordance with IEC 61034
Flame resistance	yes
Resistance to oil	Not resistant to oil, gasoline, acids, and lyes
Halogen-free	complying with IEC 60754-1/2
Behavior in fire	No corrosive or toxic fumes
Standards/specifications	IEC 61300-3-4 RL: IEC 61300-3-6

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab “Downloads”, Category “Manufacturer's declaration”

Classifications

eCl@ss

eCl@ss 10.0.1	27061003
eCl@ss 11.0	27061003

FO patch cable - FOC-ST:PA-ST:PA-OM2:D01/2 - 1115557

Classifications

eCl@ss

eCl@ss 9.0	27061003

UNSPSC

UNSPSC 18.0	26121604
UNSPSC 19.0	26121604
UNSPSC 20.0	26121604
UNSPSC 21.0	26121604

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC	EAC	B.01687

Phoenix Contact 2021 © - all rights reserved
http://www.phoenixcontact.com