

Features

- Set composed by 8 pieces tools:
 - 1 Medium head flush cutter
 - 1 Medium head nose pliers
 - 4 Tweezers
 - 2 Screwdrivers
- Ergonomic ant-slip bi-component handle for a safe, light and comfortable grip.
- Anti-reflection phosphating surface treatment.
- Open roll dimensions: 295x210x10 mm.
- Weight: 330 g
- Laser marking.

RS PRO 8 pieces Tools set: 1 MEDIUM cutter, 1 MEDIUM pliers, 4 tweezers and 2 screwdrivers

RS Stock No.: (0429664)



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- This tools set is ideal for applications in microelectronics, jewellery making, laboratory, watch making and repairs, DIY.
- Tools are made in Italy with high carbon steel and undergo a controlled atmosphere heat treatment and equipped with a return spring designed to have a constant force.
- The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator.
- Tweezers are anti-magnetic, with good corrosion resistance to most chemicals, acid and salt materials. Made from austenitic stainless steel.
- Screwdrivers are made from Chromo-Vanadium-Molybdenum steel blades with black tips having a black oxide treatment with ergonomic bi-component handles. Rotating cap.

RS PRO Medium head flush cutter

RS PRO Medium head needle nose pliers

238-0688 – RS PRO Tweezers with flat rounded tips

238-0709 – RS PRO Tweezers with very fine curved tips

238-0711 – RS PRO Tweezers with straight flat and rounded tips

238-0683 – RS PRO Tweezers with serrated, bent tips and finger grooves

249-8662 – RS PRO Slotted precision screwdriver

249-8664 – RS PRO Phillips precision screwdriver

General Specifications

RS PRO Flush cutter

Quantity	1pc
Cutter Type	Flush cut.
Tip Style	Medium head size.
Cutting capacities	Ø 1.30 mm (16 awg) copper wire
Cutting force	3 kg
Steel thickness	2.5 mm
Blade Angle	27°
Overall Length	138 mm
Net weight	65 g +/- 3 g
Type of material	high carbon steel
ESD safe	NO
Handle colour	red/black

RS PRO Serrated Nose Pliers

Rev. 01_2021

Quantity	1pc	
Plier Type	Nose Pliers	
Tip Style	Flat, serrated jaws	
Hardness	48-50 HRC	
Nose Width	3 mm	
Nose Length	20 mm	
Overall Length	146 mm +/-3 mm	
Net weight	70 g +/-3 g	
Type of material	high carbon steel	
ESD safe	NO	
Handle colour	red/black	
238-0688 – RS PRO Tweezers with flat rounded tips		
Quantity	1pc	
Tip Style	Straight flat rounded	
Serrated internally	NO	
Overall length (mm)	120	
Overall length (")	4 3/4"	
Net weight	16 g +/- 3 g	
Material	Low carbon austenitic steel	
Version	SA	
Anti-magnetic	Yes	
Anti-acid	Yes	
ESD safe	NO	
238-0709 - RS PRO Tweezers with very fine curved tips		
Quantity	1pc	
Tip Style	Curved very fine	
Serrated internally	YES	
Overall length (mm)	120 mm	
Overall length (")	4 3/4"	
Net weight	15 g +/-3 g	
Type of material	Low carbon austenitic steel	
ESD safe	NO	
Version	SA	
Anti-magnetic	Yes	
Anti-acid	Yes	

238-0711 - RS PRO Tweezers with strong and fine tips

Quantity	1pc
Tip Style	Strong fine
Serrated internally	NO
Overall length (mm)	130 mm
Overall length (")	5"
Net weight	18 g +/-3 g
Type of material	Low carbon austenitic steel
ESD safe	NO
Version	SA
Anti-magnetic	Yes
Anti-acid	Yes

**238-0683 – RS PRO Tweezers with serrated, bent tips and finger grooves**

Quantity	1pc
Tip Style	Bent
Serrated internally	YES
Serrated handles	YES
Overall length (mm)	160
Overall length (")	6 1/4"
Net weight	27 g
Material	Low carbon austenitic steel
Version	SA
Anti-magnetic	Yes
Anti-acid	Yes
ESD safe	NO



249-8662 - RS PRO Slotted precision screwdriver

Quantity	1pc
Tip	Slotted
Ø of the blade	2.5 mm
Tip length	2.5 mm
Tip width	0.4 mm
Length of the blade	75 mm
Overall length (mm)	178 mm +/-1 mm
Net weight	18 g +/-3 g
Dimensions	2.5x75 mm
Type of material	Chromo-Vanadium-Molybdenum steel blades with black tips having a black oxide treatment
ESD safe	NO
Handle colour	Red/black

**249-8664 - RS PRO Phillips precision screwdriver PH-00**

Quantity	1pc
Tip	Phillips
Ø of the blade	2.5 mm
Tip length	2.5 mm
Tip width	PH-00
Length of the blade	60 mm
Overall length (mm)	165 mm
Net weight	18 g +/-3 g
Dimensions	PH-00 2.5x60 mm
Type of material	Chromo-Vanadium-Molybdenum steel blades with black tips having a black oxide treatment
ESD safe	NO
Handle colour	Red/black

