

NSG „uClean“ Series

UCLEAN 1432 HK 110V



The universal cleaner 110V for wet and dry cleaning of buildings (commercial and residential), garage, household... . With accessory set HK house/hobby, which can be safely stored on the container. User-friendly due to a large footswitch ON/OFF and parking position for the accessory. With additional blowing function. 215 KM/H



Order no. 016238

Scope of delivery

Accessory set	HK House / Hobby
Additional filter	1 x FSS 1200 (foam material), Art. no. 413297
Filter bag	1 x FBV 25-35, Art. no. 411231 (5 pcs)

Features

Main filter	FP 3600 cellulose, dust retention capacity 99,8%, Art. no. 411729
Pulse filter cleaning	no
Appliance socket	no
Speed controller	no
Noise reduction	no
Blowing function	yes
Carry handle with cable hook	yes
Hose fixing	yes
Hose winding and connector fixture	yes
Park position	yes
Gentle start	no
After-running	no
Water level detection	yes
Antistatic prepared	no
Push handle	no
Rubber wheels and castors	no
SmartStop	no
Accessory storage	yes

Technical specifications

Power consumption (max.)	1400 Watt
Volume flow (max.)	69 l/s
Vacuum (max.)	259 mbar
Container volume (max.) Gross-Dust-Water	32/28/21 l
Sound pressure level	72.5 db(A)
Dimensions L/W/H	39,5 x 39 x 64 cm
Weight	8.1 kg
Power cable length	8,0 (PVC, red) m
Reach	9,75 - 10,75 m