


Art.-No.	VE	PG	EAN
234502008	1	132	 4 008224 619059

DUOversal Plus, 6=12, with overvoltage filter, optical overvoltage indicator in case of a fault, all sockets with connection option for one grounding-type plug or two euro-plugs, with illuminated switch (2-pole), with shutter, with 35° turned sockets, 52mm distance between sockets, cable H05VV-F3G1,5mm², 1,4m, mountable, 16A, 250V~, white



Technical data		234502008
Housing shape	Rectangular	
Colour	White	
Degree of protection (IP)	IP20	
Angle rotated central insert	35°	
Number of socket outlets with protective contact	6	
Number of Euro socket outlets	12	
Over voltage protection	Yes	
Nominal current	16A	
Core cross section	1.5mm²	
With cover	No	
Transparent	No	
Length of power cord	1.4m	

