



Product data sheet

Power tools for trade & industry

Screwdriver

VDE Screwdriver TX40x125

Insulated, simple, convenient – Bosch Professional VDE TX40x125 screwdriver

The most important data

Part Number 1 600 A02 ND0



Technical data

Technical data

Material	S2
Profile	TX
Shaft length	125 mm
Blade diameter	8 mm
Handle diameter	38 mm
Weight	0.14 kg
Anti roll-off design	+
Soft grip handle	+
Ergonomic grip	+
Tool finder	+
Slim blade insulation	+
VDE	+
Packaging dimensions (width x length x height)	63 x 307 x 38.5 mm
Maximum voltage	1,000 V

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Tested up to 10,000 volts and VDE-certified up to 1,000 volts according to DIN EN/IEC 60900
- Precise and durable with slim shaft and robust tip for fitting accuracy
- Hand-friendly and comfortable to use thanks to soft grip and ergonomic design



SOFT GRIP



ERGONOMIC



ANTI-ROLL



GS



DURABLE TIP



1.000 V



1.000 V



SLIM SHAFT



DIN EN/IEC 60900