

Han HPR SP3 Hood



Image is for illustration purposes only. Please refer to product description.

Part number	19 40 033 0414
Specification	Han HPR SP3 Hood
HARTING eCatalogue	https://harting.com/19400330414

Identification

Category	Hoods / Housings
Series of hoods/housings	Han [®] HPR
Type of hood/housing	Hood

Version

Size	SP3
Version	Top entry
Number of cable entries	1
Cable entry	1x M50
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments
Details	Please note that the use of the protection cover is needed to protect the Han [®] HC 650 / HC 800 when dropped acc. IEC 61984.

Technical characteristics

Tightening torque	4 Nm Locking screw
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	650 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140830738
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466