

Datasheet

Art-no 832-060



General Features:

- Unique forked tip (patented for) gives unsurpassed selectivity and reduces the risk of spurious indications.
- Live cables can easily be detected in equipment cabinets, fuse boxes etc.
- Extremely safe when measuring in junction boxes.
- Powerful red light in the tip to indicate voltage.
- Fully insulated for safe use.

The Volt Stick PRO, with its forked tip (patented), has an unsurpassed voltage range and increased selectivity. This is because the maximum sensitivity is between the two prongs of the fork. Outside the fork the sensitivity is low, so external interference fields have small effect.

Technical Specifications:	
Voltage range:	230 VAC
Power supply:	2 x AAA (LR03) batteries (included)
Altitude:	< 2000 m
RH:	80% @ 30°C, 50% @ 40°C
Operating temp:	-10° - +50°C
Overvoltage:	CAT III 1000V
Weight:	40g
Dimensions:	146 mm x Ø max 18mm
Approvals:	CE IEC 61010-1
Material:	Pa6, PP COP

