



## Datasheet

ENGLISH

# RS PRO FR60 Clear PP Tape

Stock No: 223-1092



### Technical Specifications:

Description: Double Side PP Tape Brown Liner	Tensil Strength: 20-30N/CM
Adhesive: Coated with Hotmelt Adhesive	Rolling ball tack:> 10(Ball no.)
Carrier: Brown Liner	Elongation: 19%
Total Thickness: 0.16 - 0.17mm	Holding power:> 2hours
Adhesive to Steel: 25-50oz/CM	Service temperature range: -15°C -> + 60°C

[rspro.com](http://rspro.com)

## **Features & Benefits:**

- **Carpet Use**
- **Hole Closure, repairing and masking**
- **Interior and exterior use**
- **packaging, holding and bundling**

### Application:

Temperature: between 0°C and + 35°C. Surface must be clean and free from dust and grease. Avoid touching the tapes exposed adhesive surface in order to keep full adhesive performance. Pressure sensitive adhesive must be applied with a maximum of pressure in order to achieve maximum pressure level. The indicated level of performance will be reached after a bonding period of 24 HRS at 23 °C.

### Storage and shelf-life:

Clean and dry in a well ventilated area, preferably at a temperature between 10°C and 30°C. Stored under these conditions shelf life will be a minimum of 6 months.



[rspro.com](http://rspro.com)

