

**1651DGTB**
**Digital vernier, reading to 0.01 mm**

CE

UNI EN ISO 13385-1DIN

**Features:**

- Reading to 0.01 mm
- Screw slider locking
- Mm/inch conversion
- Zero setting at any position
- Square depth rod up to 300 mm
- In hard plastic case

|                  | art.         | A Max<br>mm | L<br>mm | B<br>mm | G<br>mm     | HxS<br>mm |
|------------------|--------------|-------------|---------|---------|-------------|-----------|
| <b>016510211</b> | 1651DGTB 150 | 150         | 235     | 40      | 0,01-0,0005 | 16x3      |
| <b>016510212</b> | 1651DGTB 200 | 200         | 285     | 50      | 0,01-0,0005 | 16x3      |
| <b>016510213</b> | 1651DGTB 300 | 300         | 400     | 60      | 0,01-0,0005 | 16x3      |

