

PRODUCT-DETAILS

# TC95

## ROUTING CLAMP NAT NY .25IN MTG HOL



### General Information

Extended Product Type	TC95
Product ID	7TAG009710R0009
EAN	5414363059387
Catalog Description	ROUTING CLAMP NAT NY .25IN MTG HOL
Long Description	Mechanical-Locking Routing Clamp, Natural Nylon 6.6 for Temperatures up to 85 Celsius (185 F), Length of 19.1mm (0.75 Inches), Width of 12.7mm (0.50 Inches), Height of 22.6mm (0.89 Inches), Mounting Hole Size of 6.35mm (0.25 Inches), Clip or Glue Mounting Method

### Ordering

EAN	5414363059387
UPC	786210826202

### Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	1000 piece
Package Level 2 Width	11 in 279 mm
Package Level 2 Height	11.1 in 282 mm
Package Level 2 Depth / Length	13.7 in 348 mm

---

## Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19750325
Material	Nylon/Polyamide 6.6
Mounting Type	Push Mount
Number of Batteries	0
Product Name	PLASTIC CLAMP
Product Type	Mechanical-Locking Routing Clips
Special Functions	Clamp acts as a retainer during wire routing, and as a permanent clamp when desired.

---



---

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC95
Instructions and Manuals	TC95
REACH Declaration	9AKK107992A8790
RoHS Information	9AKK107992A8804

---



---

## Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121705
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5049 >> Cable clamp and staple

---



---

## Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

