



Contactor 40A, 4NO, 230V

ESC440

Technical Properties

Type of contacts	4NO
Override	No
Rated current	40 A
Rated operational voltage Ue	400 V
Frequency	50 Hz
type of connection	with screw
Connection cross-sect. rigid cable	4 / 25mm <sup>2</sup>
Connection cross-sect. flexible cable	4 / 16mm <sup>2</sup>
Command voltage AC	230 V
Rigid cable connect. cross-sect. for control	1 to 10 mm <sup>2</sup>
Max cable connect. cross section (flexible) for control	1 to 6 mm <sup>2</sup>
Inrush power absorbed	60 W
Operating consumption	7 W
Number of mechanical operations	1000000
Electric endurance in number of cycles	30000
Operating temperature	-10 to 50 °C
Storage temperature	-40 to 80 °C
Protection class	isol.class II
Protection index IP	2
Number of modules	3