

Technical data sheet

Article number:
924-00448

FDF1-4

Product Group	Female Bullet Funnel Entry
Product Family	Double Grip Pre-Insulated Terminals
Material	Brass (BS), Polyvinylchloride (PVC)
Colour	Red (RD)

Application Range	Low Voltage
Conductor Size Range mm²	0.5-1.5 mm ²
Diameter (D)	4.3 mm
Length (L)	25 mm
Length (L2)	10.5 mm
Max Current	10 A
Max Voltage	300 V
Operating Temperature	+75 °C
Package Content	100 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
Ø (D2)	4.65 mm
Ø (D3)	7.8 mm
ROHS compliant	Yes

