

# QDA32125

## MOLDED CASE CIRCUIT BREAKER 240V 125A



Download your QDA32125 datasheet



[Characteristics](#) | Documents & Downloads

### Main

Hide

<b>Product or component type</b>	Circuit breaker
<b>Range of product</b>	PowerPact Q
<b>[In] rated current</b>	125 A
<b>Product certifications</b>	CSA IEC UL listed
<b>[Ue] rated operational voltage</b>	240 V AC
<b>Mounting mode</b>	Plug-in
<b>Poles description</b>	3P
<b>Breaking capacity</b>	25 kA 240 V AC
<b>Electrical connection</b>	Lugs on load : AWG 4...300 kcmil (aluminium/copper) I-Line connection on line ABC connection
<b>Trip unit technology</b>	Thermal-magnetic
<b>Magnetic hold current</b>	1200 A
<b>Magnetic tripping current</b>	2400 A

### Offer Sustainability

Hide

<b>Sustainable offer status</b>	Green Premium product
<b>RoHS (date code: YYWW)</b>	Compliant - since 1413 - Schneider Electric declaration of conformity
<b>REACH</b>	Reference not containing SVHC above the threshold
<b>Product environmental profile</b>	Available <a href="#">download Product environmental</a>
<b>Product end of life instructions</b>	Need no specific recycling operations

### Contractual warranty

Hide

<b>Period</b>	18 months
---------------	-----------