

18V IMPACT WRENCH



DTW450RMJ

Battery Type:	Lithium-ion
Battery Quantity (3.0 Ah):	0
Voltage:	18v
Battery quantity (4.0Ah):	2
Impacts:	2200ipm
Drive Square:	1/2"
Noise sound pressure:	94dB(A)
Noise sound power:	105dB(A)
Noise K factor:	3dB(A)
No Load Speed:	1600rpm
Max Torque:	440Nm
Vibration: Fastening Bolt:	19m/sec ²
Vibration K factor:	1.5m/sec ²
Net weight:	3.1 - 3.4kg



- 4 pole motor.
- Lithium-ion batteries have greater life spans than their Ni-MH or Ni-Cad counterparts giving 430% greater run time.
- Lithium-ion's 40% weight saving means 18 volt power can be obtained by a battery that weighs the same as a 12 volt Ni-MH battery.
- High comfort grips.
- LED job light with afterglow.
- Trigger is a forward and reverse rocker switch.
- Shock absorbing battery housing.