



Utility fuse-link, low voltage, 250 A, AC 415 V, BS88/J, 31 x 131 mm, gL/gG, BS



Powering Business Worldwide™

Catalog No. 250MJ31-7

Delivery program

Product range			Fuse
Basic function			Utility fuse-link
Field of application			low voltage
Rated current	I	A	250
Rated voltage			AC 415 V
Construction size			BS88/J
Size			31 x 131 mm
Utilization category			gL/gG
Description			92 mm fixing centres
Breaking Capacity		kA	80
usable for size/applications			feeder pillars
Standard/Approval			BS
Shape			dual bolted tags (slotted)
Standards/Regulations			BS88-2 IEC 60269-2
Optional accessories			fuse-holder JW4

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	250
Rated voltage		V	415
Voltage type			AC
Rated switching capacity		kA	80
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No