

Features

- Adapter E-2000™
- 2 Philips head screws M2 x 8, blue galvanized
- IEC 61754-15
- Material steel: X10CrNi18-8 (1.4310) / plastic: PBT, fiber-glass reinforced (halogen-free)

RS PRO Adapter E2000/APC Sx LSH R&M flanged - green/green Zr sleeve Grade C

RS Stock No.: 0794582

Front



Back



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

E-2000™ adapter (LSH) singlemode (SM) in acc. with IEC 61754-15 and EN 186270. Adapter body plus flange and integrated quick-mounting clip and M2 thread, color metallic, material X10CrNi18-8 for screw mounting. Housing green (singlemode (SM) APC 8°), material PBT / UL 94 V-0, zirconia (ceramic) alignment sleeve, integral self-closing metal laser protection flaps, semi-transparent plastic dust covers, allowing optical testing with test lasers without removing the covers. The adapter qualified in accordance with IEC 61753-1 for category U (uncontrolled environment).

General Specifications

Fiber type	Singlemode (SM)
Number of connectors (A)	1
Connector color (A)	green
Polishing plug (A)	APC 8°
Attenuation grade IL (A)	C
Connector class	adapter
Dimensions	67.7 mm x 22.0 mm x 9.35 mm

Technical Specifications

Operation Temperature	-40°C to +85°C
Mating Durability	1000 mating cycles

Approvals

Declarations	MFR Declaration of Conformity
Hazardous Area Certification	Conforms to TIA/EIA 492AAAA, IEC60793-2-10 A1b
Standards Met	acc. to IEC 61754-15, acc. to DIN EN 186270, UL Listed