







ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE
	B	ECN # 040716-1 CHANGE PACKING	07/16/04'
 *	C	ECR # 080303-1 ADD ROHS,EDIT CONN,PACKING	03/03/08'
 *	D	ECR # 080520-1 EDIT PACKING,ADD BARCODE NO.	05/20/08'



NOTE:

- HOOK UP WIRE : UL1007 18AWG COLOR:YELLOW, BLACK, RED
- CONNECTOR :
 P1 : 15 PIN SATA SOCKET CRIMP TYPE GOLD FLASH CONTACT 
 P2 : 4 PIN MATE LOCK MALE .
 HOUSING: JWT P/N: C5081H02-4P 
 TERMINAL: JWT P/N: C5081T0B-2 .


- HOOD: P1: MOLDED TYPE, PVC 45P, COLOR:BLACK(NK-K01)
- ELECTRICAL TEST: <1>100% OPEN SHORT & MIS WIRE TEST.
 <2>CONTACT RESISTANCE 3 Ohms MAX
 <3>INSULATION RESISTANCE 20M Ohms MIN

- PACKING: EACH PC / POLYBAG + HEADER CARD(FDRAG04)+P/N LABEL
 50 PCS / INNER CARTON WITH OUTER CARTON LABEL,
 INNER CARTON SIZE: 230*220*120mm,
 6 INNER CARTONS / MASTER CARTON,
 MASTER CARTON SIZE: 460*380*245mm.



 6.BAR CODE NO.: 7611990148547.

	P1		P2
	1, 2, 3	<u>YELLOW</u>	1
	4, 5, 6	<u>BLACK</u>	2
	7, 8, 9	<u>RED</u>	4
	10, 11, 12	<u>BLACK</u>	3

Tolerance Inch M/M				
.X	.015	.30		
.XX	.010	.10	Title	
.XXX	.005	.05	SERIAL ATA POWER SUPPLY CABLE	
Draw FANNIE 05/20/08'			Customer P/N: 11.03.1055	
Check			App'd	Customer T-RAG
Engr			Scale NONE	Units m/m
			Third Angle Projection 	
			Dwg No. 150-0327	REV:D Sheet 1/1

