

Heater Series CS 060

Art.-No. 06020.1-00

(Standard version: 06020.0-00)

Important data



1. Mecha. data¹⁾

Housing: no difference

Connection/cable: no difference

2. Technical data¹⁾

Operating voltage: 24V AC/DC (min 12V; max. 28V)²⁾

Heating capacity: no difference
(150W)

Inrush current max.: 16.0A

Operating temperature: -20 to +70°C (-4 to +158°F)

Pre-fuse: 10A T (time-delay)

Air outlet temp.: tbd

Approval: VDE; EAC

¹⁾ data that vary compared to the standard version

²⁾ Operating with voltages below 15V AC/DC reduces heating performance by approx. 10%.