

Manifold sub-base with angled connections NAVW-3/8-NPT-2

Part number: 152793

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width	135 mm
Mounting position	optional
Operating pressure	0 MPa ... 1.6 MPa
Operating pressure	0 bar ... 16 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Ester oil < 0.1mg/m³, according to ISO 8573-1:2010 [-:-:2]
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-20 °C ... 80 °C
Media temperature	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Mounting method for sub-base	With through-hole
Type of mounting	With through-hole
Pilot air port 12/14	1/8 NPT
Auxiliary pilot air port 12	1/8 NPT
Auxiliary pilot air port 14	1/8 NPT
Pilot air port 12	1/8 NPT
Pilot air port 14	1/8 NPT
Pneumatic connection, port 1	3/8 NPT
Pneumatic connection, port 2	3/8 NPT
Pneumatic connection, port 4	3/8 NPT
Material sub-base	Die-cast aluminium