



Main

Range of product	Lineryg
Product or component type	Cable end
Cable end size	Medium
Standards	DIN 46228-1
Type of packing	Individual bag
Quantity per set	Set of 100
Cable cross section	10 mm ²

Complementary

Cable end type	Single conductor
Additional information	Non-insulated
Bezel material	Halogen-free plastic
Tube material	Copper conforming to ISO 1337
Number of cables	1
AWG gauge	AWG 8
Bezel size	Ø 5.8 mm
Tube diameter	4.5 mm
Length	18 mm
Tube length	18 mm

Environment

Ambient air temperature for operation	-20...105 °C
---------------------------------------	--------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0607 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Need no specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.