


Product data sheet

LRCB 20

Shaft support with bore holes



β [°]:	50
A [mm]:	52
d [mm]:	20
H [mm]:	32
H1 [mm]:	6
J [mm]:	100
J1 [mm]:	37
L [mm]:	600
M [mm]:	8.3
N [mm]:	6.6
N1 [mm]:	6.6

Date: 27/05/2020

The contents of this report are the copyright of the publisher and may not be reproduced (even extracts) unless permission is granted. Every care has been taken to ensure the accuracy of the information contained in this report but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

Product data sheet

LRCB 20

Shaft support with bore holes

Screw:	M6X25
Weight [kg]:	0.92

Date: 27/05/2020

The contents of this report are the copyright of the publisher and may not be reproduced (even extracts) unless permission is granted. Every care has been taken to ensure the accuracy of the information contained in this report but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.