



## Polycarbonate Bulkhead Black



- Bulkhead suitable for commercial applications (supplied less lamp)
- Vandal resistant all polycarbonate construction

### General Information

Lamp Type	E27
IP Rating	IP65
IK Rating	IK07
Class Protection	2
Internal / External	Internal / External
Surface / Recessed / Suspended	Surface
Warranty (Years)	4
Material	Polycarbonate

### Technical Information

Wattage	100W
Input	220/240V
Hertz	50/60Hz
Operating Temp	5°C to 25°C



