

Juniper EX-SFP-10GE-LR Compatible SFP+ Module - 10GBASE-LR - 10GbE Single Mode Fiber SMF Optic Transceiver - 10GE Gigabit Ethernet SFP+ - LC 10km - 1310nm - DDM

Product ID: EXSFP10GELRS



The EXSFP10GELRS is a Juniper EX-SFP-10GE-LR compatible fiber transceiver module that has been designed, programmed and tested to work with Juniper brand switches and routers. It delivers dependable 10GbE connectivity over fiber cable, for 10GBASE-LR compliant networks, with a maximum distance of up to 10 km (6.2 mi).

Technical Specifications:

- Wavelength: 1310nm
- Maximum Data Transfer Rate: 10 Gbps
- Type: Singlemode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 10 km (6.2mi)
- MTBF: 2,104,865 hours
- Power Consumption: Less than 1.3 Watts
- Digital Diagnostics Monitoring (DDM): Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

- Replacing defective or damaged SFP+ modules in Juniper switches and routers
- Expand your network to remote segments

Features

- **100% JUNIPER EX-SFP-10GE-LR COMPATIBLE SFP+ TRANSCEIVER:** Designed, programmed and tested to work with compatible Juniper switches and routers to deliver reliable 10GbE connectivity
- **TECHNICAL SPECS:** 10GBASE-LR 10Gbps Single Mode (SMF) LC Connector 1310nm Digital Diagnostic Monitoring (DDM) Distances up to 10km (6.2mi)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Juniper routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance.

Hardware

Warranty	Lifetime
Compatible Brand	Juniper

Performance

Maximum Data Transfer Rate	10 Gbps
Max Transfer Distance	10 km (6.2 mi)
Type	Single Mode
Wavelength	1310nm
Fiber Operating Mode	Full-Duplex
DDM	Yes

Compatible Networks	10 Gbps
MTBF	2,104,865 hours
Power Consumption (In Watts)	< 1.2 W

Connector(s)

Local Unit Connectors	1 - Fiber Optic LC Duplex
-----------------------	---------------------------

Special Notes / Requirements

Note	For use in 10 Gigabit fiber networking equipment and media converters
------	---

Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-40C to 85C (-40F to 185F)
Humidity	5~95% RH

Physical Characteristics

Color	Silver
Product Length	2.3 in [58.4 mm]
Product Width	0.5 in [1.4 cm]
Product Height	0.5 in [1.3 cm]
Weight of Product	0.7 oz [21.0 g]

Packaging Information

Package Length	4.4 in [11.3 cm]
Package Width	3.7 in [9.3 cm]
Package Height	1.3 in [3.3 cm]
Shipping (Package) Weight	1.8 oz [50.0 g]

What's in the Box

Included in Package	1 - SFP+ transceiver
---------------------	----------------------

**Warranty
Information**

Warranty

Lifetime

**Product appearance and specifications are subject to change without notice.*