

Datasheet

RS PRO GRP Ex Polyester Enclosure black, IP66, ATEX

Stock No: 2131650



Technical Specifications:

| | |
|-------------------|------------------------------------------------------------------------------------------------|
| Material | Glasfibre reinforced polyester |
| Colour | RAL 9011, black |
| Dimension | 120 x 220 x 91 mm (HxWxL) |
| IP rating | IP66 |
| NEMA | 1, 3S, 4 |
| Impact resistance | IK 09 in reference to EN 60068-2-75 |
| Seal | Silicon seal |
| Temperature range | -50° up to +125°C |
| Approvals | ATEX, IEC Ex and EAC U-approved UL 508 A, Maritime Register of shipping, Lloyds register |

Features & Benefits:

- incl. in delivery: base, lid, seal, captive +/- stainless steel screws, 4 cooper plated earthing screws
- Ex-U approved enclosure for all chemical and hazardous atmospheres
- good UV resistance
- good chemical resistance
- halogenfree material
- watertight solution for outdoor and indoor application

Dimensional line drawings

