

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0194180040

Status:

Active

Overview:

MX150L Industrial Sealed Connector System

Description:

MX150L 16 Circuit Receptacle for 18-22 AWG Wire, without CPA



Series image - Reference only

Documents:	
3D Model	Packaging Specification PK-19418-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19417-001-001 (PDF)	Product Literature (PDF)

Agency Certification	
CSA	LR18689
UL	E152602
General	
Product Family	Crimp Housings
Series	19418
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
Overview	MX150L Industrial Sealed Connector System
Product Literature Order No	987650-2181
Product Name	MX150L
UPC	822348526505
Physical	
Circuits (maximum)	16
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Net Weight	36.597/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Electrical	
Current - Maximum per Contact	18.0A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-19418-001
Product Specification	PS-19417-001-001
Sales Drawing	SD-19418-007

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
ED/61/2018 (27 June 2018)
Acetamide, N-methyl-
Dinoseb
furan
C,C'-
azodi(formamide)
tricosafuorododecanoic
acid
heptacosafuorotetradecanoic
acid
methoxyacetic acid
1,2-diethoxyethane
henicosafuoroundecanoic
acid
sodium
peroxometaborate
pentacosafuorotridecanoic
acid
3-ethyl-2-methyl-2-
(3-methylbutyl)-1,3-
oxazolidi
Hydrazine
Disodium tetraborate
Boric acid
HBCDD
Trixylyl phosphate
4-(1,1,3,3-
tetramethylbutyl)phenol,
ethoxylated
Sodium perborate;
perboric acid, sodium
salt
Ethylenediamine
dodecamethylcyclhexasiloxane
1,3-Propanesultone

China RoHS

2,4-Di-tert-butyl-6-(5-chlorobenzotriazol-2-yl)p
Perfluorohexane-1-sulphonic acid and its salts
propylene oxide
nitrobenzene
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o
Perfluorononan-1-oic acid
(2,2,3,3,4,4,5,5,6,6,7
Silicic acid (H₂Si₂O₅),
barium salt (1:1),
lead-
Trichloroethylene
1,2,3-
Trichloropropane
1,2-dichloroethane
1-bromopropane
Dibutylphthalate (DBP)
Di-(2-ethylhexyl)phthalate (DEHP)
2,4-dinitrotoluene
Tris(2-chloroethyl)phosphate
Boric acid, disodium salt, hydrate
1-Methyl-2-pyrrolidone
formamide
4,4'-bis(dimethylamino)benzophenone
N,N,N',N'-tetramethyl-4,4'-methyldianiline
1,2-bis(2-methoxyethoxy)ethane
[4-[4,4'-bis(dimethylamino)benzhydrylidene]cycl
4,4'-bis(dimethylamino)-4''-(methylamino)trityl
Diboron-trioxide
[4-[[4-anilino-1-naphthyl][4-(dimethylamino)phen
α,α#Bis[4-(dimethylamino)phenyl]-4
(phenylamino)
diethyl sulphate
Halogen-Free
Status
Low-Halogen
Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

	ELV	Not Relevant
	Prop65	Compliant
	RoHS Phthalates	Not Contained
<div><div>Search Parts in this Series 19418 Series</div><div>Mates With 19419 Plug, 19429 Panel Mount Plug</div><div>Use With 19420 Female Crimp Terminal</div></div>		

This document was generated on 09/11/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION