



ENGLISH

Datasheet

## RS Pro NiMH D Rechargeable Battery, 8000mAh

RS Stock No: **504-6089**



### Product Details

RS Pro NiMH rechargeable battery of AAA size, has 8000 mAh of battery capacity to power up a device. This battery has a nominal voltage of 1.2 V and is suitable for general purpose applications. The battery is perfect to work within the temperature range of -10 to +60°C.

### Features and Benefits

- D size
- NiMH rechargeable battery
- 8000 mAh battery capacity
- 1.2 V of nominal voltage
- Suitable for general purpose applications



ENGLISH

### Specifications:

Chemistry	NiMH
Size	D
Terminal Type	Standard
Capacity	8000 mAh
Dimensions	32.2 x 61.5 mm
Maximum Continuous Current	3 mA
Maximum Operating Temperature	+60°C
Minimum Operating Temperature	-10°C
Nominal Voltage	1.2 V
Operating Temperature Range	-10 to +60°C
Size	D