

S-11 ; 0 ... 0.25 bar; 4...20 mA, 2-W

Pressure transmitter for general applications

Item number:	9021264	
Quantity:	1 pcs.	
Order code:	S-11-A-BAN-85-Q1ZGA4ZAZ-ZZZ ZFOSE3	W101Z-ZZ-F2ASZZ-
Overview:	S-11 ; 0 ... 0.25 bar; 4...20 mA, 2-W @ 10 ... 30 V DC; Accuracy: 0.5% of span G 1 B flush diaphragm with O-ring Wetted parts: stainless steel Sealing: NBR; 4-pin L-plug DIN EN 175301-803, IP65 U+=1, U-=2 Permissible medium temperature: -30 ... +100 °C (-22 ... +212 °F) Specifications according to data sheet: PE 81.02	
Details:	Pressure transmitter for general applications Model S-11 with flush diaphragm Specifications according to data sheet: PE 81.02 Power supply: DC 10 (14) ... 30 V Case: stainless steel Output signal: 4 ... 20 mA, 2-wire Measuring range: 0 ... 0.25 bar Process connection: G 1 B flush diaphragm with O-ring Wetted parts: stainless steel Sealing: NBR Accuracy: 0.5% of span Electrical connection: 4-pin L-plug DIN EN 175301-803, IP65 Permissible medium temperature: -30 ... +100 °C (-22 ... +212 °F) Power supply: 10 ... 30 V DC Pin assignment: U+=1, U-=2 shield: standard WIKA standard - specification according to data sheet Test protocol: without test protocol Certificates: without Import documentation CIS-States: without	