

Savi® W710-M
Savi® W720-M
Multi-Device Wireless
Headset System


OPTIMIZED FOR
Microsoft® Lync™

Guía de inicio rápido
Guide de démarrage rapide

QUICK START GUIDE

VIDEO GUIDE
<http://docs.plantronics.com/savi-700>

plantronics®



- 1 **Decrease volume** Short press –
- 2 **Answer/end call** Short press
- 3 **Mute** Short press
- 4 **Increase volume** Short press +

Flash While on call, long press volume up + or volume down – for 1.5 seconds, will put call on hold and answer another.

CAUTION For your safety, do not use headset at high volumes for extended periods of time. Doing so can cause hearing loss. Always listen at moderate levels. For more information on headsets and hearing visit plantronics.com/healthandsafety.

Please refer to the separate safety instructions for important product safety information prior to installation or use of the product.
Savi W710/W720 has a WO2 base and a WH300/WH350 headset.
pn89312-01 (01.13) am89313-01


Savi® W710-M
Savi® W720-M
Sistema de audífono
inalámbrico de dispositivo
múltiple

OPTIMIZED FOR
Microsoft® Lync™

GUÍA DE INICIO RÁPIDO

GUÍA DE VIDEO
<http://docs.plantronics.com/savi-700>

plantronics®



- 1 **Bajar el volumen** Presione brevemente –
- 2 **Contestar/terminar una llamada** Presione brevemente
- 3 **Silencio** Presione brevemente
- 4 **Aumentar el volumen** Presione brevemente +


Flash Durante una llamada, presione por 1.5 segundos más volumen + o menos volumen – para poner la llamada en espera y responder otra llamada.

PRECAUCIÓN Por su seguridad, no use el audífono a un volumen alto durante periodos prolongados. Esto puede causar pérdida de audición. Use siempre un volumen moderado. Para obtener más información sobre los audífonos y la audición, visite plantronics.com/healthandsafety.


Antes de instalar o utilizar el producto, consulte las instrucciones de seguridad (aparte) para obtener información importante acerca de la seguridad del producto.
Savi W710/W720 tiene una base WO2 y un audífono WH300/WH350.

1 Headset
Customize and Charge


- 1 Attach charge cradle to base.



- 2 Plug one end of power supply into power jack on back of the base and other end into working power outlet.




- 3 To charge, dock headset in base, minimum of 20 minutes.




2 Desk Phone
Connect and Call

- 1 Choose desk phone setup **A, B, or C** and connect cables.
A Desk phone (standard)



USE

- B Desk phone + HL10 lifter (sold separately)**
See user guide at plantronics.com/accessories




USE

- C Desk phone + EHS cable (sold separately)**
See user guide at plantronics.com/accessories




USE

- 2 While wearing headset, short press base desk phone button.




NOTE If you don't have remote call control through a lifter (HL10) or cable (EHS), manually remove desk phone handset before each call.

- 3 If you do not hear a dial tone, open side panel and adjust middle configuration switch (A–C) until you do. Default setting **A** works for majority of desk phones.




- 4 Dial test call from desk phone.
5 End call by pressing headset call control button.



3 Mobile
Connect and Call


- 1 Press down and hold Bluetooth pairing button (4 seconds) on Savi base until indicator LED flashes red and blue.




- 2 Place Bluetooth mobile phone into search mode. Select **SAVI 7xx** from the list of found devices.




- 3 If prompted by mobile phone, type **0000** as passcode. Bluetooth indicator LED on base will turn solid blue when base has an active connection with mobile phone.



- 4 While wearing headset, short press base mobile button.




- 5 Dial test call from mobile phone.
6 End call by pressing headset call control button.




4 Computer
Connect and Call


- 1 Connect USB cable.



- 2 While wearing headset, short press base computer button.



- 3 Dial test call from computer softphone.
4 End call by pressing headset call control button.



NEED MORE HELP?

Technical support
plantronics.com/support
Online user guide
<http://docs.plantronics.com/savi-700>

2 Teléfono de escritorio
Conecte y llame.

- 1 Elija la configuración del teléfono **A, B, o C** y conecte los cables.
A Teléfono de escritorio (estándar)



USO

- B Teléfono de escritorio + dispositivo para descolgar el teléfono HL10 (se vende por separado)**
Ver guía del usuario en plantronics.com/accessories




USO

- C Teléfono de escritorio + cable EHS (se vende por separado)**
Ver guía del usuario en plantronics.com/accessories




USO

- 2 Al usar el audífono, presione brevemente el botón de la base del teléfono de escritorio.



NOTA Si no tiene un control remoto para llamadas a través de un dispositivo para descolgar el teléfono (HL10) o un cable (EHS), quite manualmente el auricular del teléfono de escritorio antes de cada llamada.

- 3 Si no escucha el tono de marcado, abra el panel del costado y ajuste el modificador de configuración media (A–G) hasta escucharlo. El ajuste preconfigurado **A** funciona para la mayoría de los teléfonos de escritorio.




- 4 Marque llamada de prueba desde el teléfono de escritorio.
5 Para terminar la llamada, presione el botón de control de llamadas del audífono.



3 Móvil
Conecte y llame.


- 1 Presione hacia abajo y mantenga presionado el botón de emparejamiento de Bluetooth (durante 4 segundos) en la base Savi hasta que el indicador LED parpadee en rojo y azul.




- 2 Coloque el teléfono móvil Bluetooth en el modo búsqueda. Seleccione **SAVI 7xx** del listado de dispositivos que se encontraron.




- 3 Si lo solicita el teléfono móvil, escriba **0000** como código de acceso. El indicador LED de Bluetooth en la base se volverá de color azul fuerte una vez que la base tenga una conexión activa con el teléfono móvil.



- 4 Durante el uso del audífono, presione brevemente el botón de la base del móvil.



- 5 Marque llamada de prueba desde el teléfono móvil.
6 Para terminar la llamada, presione el botón de control de llamadas del audífono.



¿NECESITA MÁS AYUDA?

Asistencia para productos
plantronics.com/support
Guía del usuario en línea
<http://docs.plantronics.com/savi-700>


Plantronics, Inc.
345 Encinal St
Santa Cruz, CA 95060
United States

Plantronics BV
South Point Building C
Scorpius 140
2132 LR Hoofddorp
Netherlands


© 2013 Plantronics, Inc. All rights reserved. Plantronics and Savi are trademarks or registered trademarks of Plantronics, Inc. All other trademarks are the property of their respective owners. Microsoft, Internet Explorer, Windows, Windows Vista, and Windows XP are trademarks or registered trademarks of Microsoft Corporation in the US and other countries. Pentium is a trademark of Intel Corporation in the U.S. and other countries. The Bluetooth trademark is owned by Bluetooth SIG, Inc. and any use of the mark by Plantronics, Inc. is under license. Patents U.S. 7,633,963; 5,210,791; D505,413; D535,285; D538,785; D599,331; China ZL200630123314.7; ZL200630123313.2; EM 000543798-0004; 000543798-0005; Taiwan D117515; D117333

4 PC
Conecte y llame.


- 1 Conecte el cable USB.



- 2 Al usar el audífono, presione brevemente el botón de la base de la computadora.



- 3 Marque llamada de prueba desde el softphone de la computadora.
4 Para terminar la llamada, presione el botón de control de llamadas del audífono.



Advertencia:
"La operación de este equipo está sujeta a las siguientes dos condiciones: (1) es posible que este equipo o dispositivo no cause interferencia perjudicial y (2) este equipo o dispositivo debe aceptar cualquier interferencia, incluyendo la que pueda causar su operación no deseada."

Declaration of Conformity
We Plantronics, 345 Encinal Street, Santa Cruz, California, 95060 USA (800) 544-4660, declare under our sole responsibility that the product WD2 complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

FCC Registration Information – Part 68
This equipment complies with Part 68 of the FCC rules and the requirements adopted by ACTA. On the exterior of this equipment is a label that contains a product identifier in the format US-AAAQ#TXXXX. If requested, this information must be provided to your telephone company.
A plug and jack used to connect this equipment to the telephone line may require the use of a specific device. Excessive RENS on a telephone line may result in the device not ringing in response to an incoming call. In most, but not all areas, the sum of the RENS should not exceed five (5.0). To be certain of the number of devices you may connect to your line, as determined by the REN, contact your local telephone company. For products approved after August 8, 2002, the REN for this product is part of the product identifier that has the format US-AAAQ#TXXXX. The digits represented by ## are the REN without the decimal point. (For example, 03 represents a REN of 0.3.) For earlier products, the REN is separately shown on the label.
If this telephone equipment causes harm to the telephone network, the telephone company will notify you in advance that temporary discontinuance of service may be required. But if advance notice isn't practical, the telephone company will notify the customer as soon as possible. Also, you will be advised of your right to file a complaint with the FCC if you believe it is necessary.
The telephone company may make changes in its facilities, equipment, operations, or procedures that could affect the proper functioning of your equipment. If they do, you will be notified in advance in order for you to make necessary modifications to maintain uninterrupted service.
If trouble is experienced with this unit, for repair or warranty information, please contact customer service at (800) 544-4660. If the equipment is causing harm to the network, the telephone company may request that you disconnect the equipment until the problem is resolved.
DO NOT DISASSEMBLE THIS EQUIPMENT: it does not contain any user-serviceable components. We recommend the installation of an AC surge arrester in the AC outlet to which this equipment is connected. Telephone companies report that electrical surges, typically lightning transients, are very destructive to customer terminal equipment connected to AC power sources.

Exposure to RF Radiation
The internal wireless radio operates within the guidelines found in radio frequency safety standards and recommendations, which reflect the consensus of the scientific community. Independent studies have shown that the internal wireless radio is safe for use by consumers. Visit plantronics.com for more information.
In order to comply with FCC and IC RF Exposure requirements, the base must be installed and operated such that a minimum separation distance of 20 cm is maintained between the base and all persons during normal operation.
NOTE: Modifications not expressly approved by Plantronics, Inc. could void the user's authority to operate the equipment.

Industry Canada Regulatory Information
This product meets the applicable Industry Canada technical specifications/La présent matériel est conforme aux spécifications techniques applicables d'Industrie Canada.
This Class B digital apparatus complies with Canadian ICES-003. /Cet appareil numérique de la classe B est conforme à la norme NMB-003 du Canada.
Operation is subject to the following two conditions: (1) this device may not cause interference, and (2) this device must accept any interference, including interference that may cause undesired operation of the device.

NOM-121-567-2009
Advertencia: La operación de este equipo está sujeta a las siguientes dos condiciones: (1) es posible que este equipo o dispositivo no cause interferencia perjudicial y (2) este equipo o dispositivo debe aceptar cualquier interferencia, incluyendo la que pueda causar su operación no deseada."



Savi® W710-M
Savi® W720-M


Système de micro-casque
sans fil multipériphérique

OPTIMIZED FOR
Microsoft® Lync®

GUIDE DE DÉMARRAGE
RAPIDE

GUIDE VIDÉO
http://docs.plantronics.com/savi-700

plantronics®



- 1 Réduire le volume Appuyez brièvement sur –
 - 2 Répondre/mettre fin à un appel Appuyez brièvement sur
 - 3 Discrétion Appuyez brièvement sur
 - 4 Augmenter le volume Appuyez brièvement sur +
- Commutateur** Pendant un appel, appuyez sur le bouton + ou - du volume durant 1,5 seconde pour mettre l'appel en attente et prendre un autre appel.

AVERTISSEMENT Pour votre propre sécurité, n'utilisez pas le micro-casque à volume élevé sur de longues périodes. Cela pourrait provoquer des problèmes d'audition. Conservez toujours un niveau d'écoute modéré. Pour en savoir davantage sur les micro-casques et l'audition, visitez le site plantronics.com/healthandsafety

Veuillez lire les consignes de sécurité fournies séparément avant d'installer ou d'utiliser le produit. Elles contiennent des renseignements importants relatifs à la sécurité.


Le système Savi W710/W720 comprend la base WO2 et le micro-casque WH300/WH350.

1 Micro-casque
Personnalisation et charge

- 1 Connectez le chargeur à la base.
- 2 Branchez une extrémité du cordon d'alimentation dans la prise en arrière de la base et l'autre dans une prise de courant fonctionnelle.
- 3 Pour recharger le micro-casque, connectez-le à la base pendant au moins 20 minutes.


2 Téléphone de bureau
Connexion et appel

- 1 Choisissez la configuration **A, B, ou C** pour le téléphone de bureau et connectez les câbles en conséquence.
A Téléphone de bureau (standard)
UTILISER
 - B Téléphone de bureau et décrocheur HL10 (vendu séparément)**
Consultez le guide d'utilisateur à l'adresse plantronics.com/accessories
UTILISER
 - C Téléphone de bureau et câble de commutateur électronique (vendu séparément)**
Consultez le guide d'utilisateur à l'adresse plantronics.com/accessories
UTILISER
- 2 Une fois le casque installé, pressez brièvement sur le bouton de conversation de la base reliée au téléphone.




REMARQUE Si vous ne pouvez pas contrôler vos appels à distance à l'aide d'un décrocheur (HL10) ou d'un câble de commutateur électronique, décrochez manuellement le combiné avant chaque appel.

3 Si vous n'entendez pas de tonalité, ouvrez le panneau latéral et ajustez le bouton de configuration central (A-G). La configuration par défaut **A** fonctionne avec la majorité des téléphones de bureau.







- 4 Procédez à un appel d'essai à partir du téléphone de bureau.
- 5 Raccrochez en appuyant sur le bouton de contrôle des appels du micro-casque.





3 Cellulaire
Connexion et appel

- 1 Maintenez la pression sur le bouton de couplage de la base du système Savi vers le bas pendant 4 secondes jusqu'à ce que le voyant clignote en rouge et bleu.
- 2 Mettez le cellulaire Bluetooth en mode recherche. Sélectionnez **SAVI 7xx** dans la liste des périphériques détectés.
- 3 Si le téléphone demande un mot de passe, entrez quatre zéros **0000**. Le voyant Bluetooth s'allume en bleu lorsque la base est connectée au cellulaire.
- 4 Une fois le casque installé, pressez brièvement sur le bouton de conversation de la base reliée au cellulaire.
- 5 Procédez à un appel d'essai à partir du cellulaire.
- 6 Raccrochez en appuyant sur le bouton de contrôle des appels du micro-casque.



4 Ordinateur
Connexion et appel

- 1 Connectez le câble USB.
- 2 Une fois le casque installé, pressez brièvement sur le bouton de conversation de la base reliée à l'ordinateur.
- 3 Procédez à un appel d'essai à partir du logiciel de téléphonie de l'ordinateur.
- 4 Raccrochez en appuyant sur le bouton de contrôle des appels du micro-casque.



BESOIN D'AIDE
SUPPLÉMENTAIRE?

Soutien pour les produits
plantronics.com/support
Guide de l'utilisateur en ligne
<http://docs.plantronics.com/savi-700>