

9p STR FE PL2_M3 nut_Reel_140 pcs



Image is for illustration purposes only. Please refer to product description.

Part number	09 55 115 6611 741
Specification	9p STR FE PL2_M3 nut_Reel_140 pcs
HARTING eCatalogue	https://harting.com/09551156611741

Identification

Category	Connectors
Series	D-Sub
Identification	Standard
Element	Connector
Description of the contact	Stamped Straight

Version

Termination method	Reflow soldering termination (SMT)
Gender	Female
Size	D-Sub 1
Connection type	Motherboard to daughtercard Mezzanine
Number of contacts	9
Locking type	Fixing flange with thread M3
Pack contents	140 pieces on reel

Technical characteristics

Contact spacing (termination side)	2.74 mm
Rated current	5 A
Clearance distance	≥1 mm
Creepage distance	≥1 mm
Insulation resistance	> 5 x 10 ⁹ Ω
Contact resistance	≤25 mΩ



Pushing Performance
Since 1945

Technical characteristics

Tightening torque	≤0.6 Nm Female screw lock
Limiting temperature	-55 ... +125 °C (during reflow soldering max. +240 °C for 30 s)
Insertion force	≤30 N
Withdrawal force	≥3.3 N ≤20 N
Performance level	2 acc. to CECC 75301-802
Mating cycles	≥250
Test voltage $U_{r.m.s.}$	1 kV
Isolation group	IIIa ($175 \leq CTI < 400$)
PCB thickness	≥1.6 mm
Installation height	6.35 mm
Hot plugging	No
Moisture Sensitivity Level (MSL)	1 acc. to ECA/IPC/JEDEC J-STD-020D
Process Sensitivity Level (PSL)	R0 acc. to ECA/IPC/JEDEC J-STD-020D

Material properties

Material (insert)	Liquid crystal polymer (LCP) Shell: steel, nickel plated
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	DIN 41652
----------------	-----------



Pushing Performance
Since 1945

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079

Commercial data

Packaging size	1
Net weight	848.12 g
Country of origin	Vietnam
European customs tariff number	85366990
GTIN	5713140068520
eCl@ss	27440214 D-Sub coupler
ETIM	EC001136
UNSPSC 24.0	39121469