

Gripper finger cap

HAMA-GA-B33-70-3-S-40-BU

Part number: 8203485

FESTO



 General operating condition

Data sheet

Feature	Value
Size	70
Min. ø to be gripped	55 mm
Max. ø to be gripped	80 mm
Working stroke	20 mm ... 90 mm
Number of gripper fingers	3
Design	For grippers
Design	Form-fitting Frictional locking
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
LABS (PWIS) conformity	VDMA24364 zone III
Suitable for use with food	See supplementary material information
Ambient temperature	0 °C ... 60 °C
Product weight	114 g
Colour	Blue
Shore hardness	A 40 +5
Note on materials	RoHS compliant
Gripper finger material	VMQ (silicone), metal detectable