



6008

Single-Row Deep Groove Ball Bearings



Boundary Dimensions

d	40	mm	Bore diameter
D	68	mm	Outside diameter
B	15	mm	Width
r (min.)	1	mm	Chamfer dimension

Basic Load Ratings

Cr	18400	N	Basic dynamic load rating
C0r	11500	N	Basic static load rating

Speeds

Grease	12000	min-1	Grease lubrication
Oil (Oil-bath)	14000	min-1	Oil-bath lubrication

Abutment and Fillet Dimensions

da (min.)	45	mm	Diameter of shaft abutment
da (max.)	47.5	mm	Diameter of shaft abutment
Da (max.)	63	mm	Diameter of housing abutment
ra (max.)	1	mm	Radius of shaft or housing fillet

Calculation factors

fo	15.3		Factor
----	------	--	--------

Additional information

z	12		Number of Balls
Dw	7.938	mm	Ball Diameter

Mass

Mass approx.	0.19	kg	Mass approx.
--------------	------	----	--------------

