

Ultrasonic Cleaner Specification

SOURCE:

<https://support.zortrax.com/ultrasonic-cleaner-specification/>

The following table summarizes all technical specifications and operational characteristics of the Zortrax Ultrasonic Cleaner.

Device features	
Tank dimensions	240 x 135 x 100 mm (9.4 x 5.3 x 4.0 in)
Maximum tank capacity	3.2 l (108.2 fl oz)
Material	Stainless steel
Time control	0-30 min
Weight and physical dimensions	
Device (W x D x H)	250 x 150 x 230 mm (9.8 x 5.9 x 9.1 in)
Weight	3.3 kg (7.2 lb)
Temperature	
Ambient Operating Temperature	20 – 30° C [68 – 86° F]
Storage Temperature	0 – 35° C [32 – 95° F]
Electrical	
Maximum power consumption	120 W
Cleaning frequency	40 KHz