

## FEATURES

- **2.5 m cable length:** Provides ample reach for versatile installation options
- **IEC C15 to GB 2099 connectors:** Ensures compatibility with a wide range of devices
- **10 A current rating:** Supports high-performance applications
- **250 V voltage rating:** Suitable for standard power requirements
- **Black rubber jacket:** Offers durability and protection in various environments
- **Straight plug and socket design:** Facilitates easy and secure connections

## RS PRO 2.5 m Power Cable, IEC C15 to GB 2099

RS Stock No: 558-967



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO power cable is designed for reliable and efficient power transmission, featuring a 2.5 m length for flexible connectivity. Ideal for use in environments requiring a secure connection between IEC C15 and GB 2099 interfaces, it supports a current rating of 10 A and a voltage of 250 V, ensuring robust performance.

## General Specifications

Connector Type A	IEC C15
Connector Type B	GB 2099
Jacket Colour	Black
Mains Socket Type	Straight
Product Type	Power Cable

## Mechanical Specifications

Cable Length	2.5 m
Jacket Material	Rubber

## Electrical Specifications

Current Rating	10 A
Mains Plug Type	Straight
Voltage	250 V

## Approvals

Standards/Approvals	CCCs, CSA, ENEC 11, JET, PSE, RCM N10544, UL
---------------------	--

