

Classic filament LED candles and lusters

Classic LEDCandle ND 4.3-40W B22 827 B35 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data

General Information	
Cap-Base	B22 [B22]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	4.3-40W
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	109.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	4.3 W


Lamp Current (Nom)	40 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	45 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Consumption kWh/1000 h	5 kWh

Classic filament LED candles and lusters

Product Data	
Full product code	871869680857300
Order product name	Classic LEDCandle ND 4.3-40W B22 827 B35 CL
EAN/UPC - Product	8718696808573
Order code	929001889902

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001889902
Net Weight (Piece)	0.010 kg


Dimensional drawing




Candle B35 4.3-40W 470lm 2700K B22 ND

Product	D	C
Classic LEDCandle ND 4.3-40W B22 827 B35 CL	35 mm	93 mm


Photometric data



LEDcandle CLA 4.3-40W E14 B35 Clear 827 ND




LEDcandle CLA 4.3-40W B22 B35 Clear 827 ND




LEDcandle CLA 4.3-40W E14 B35 Clear 827 ND

Classic filament LED candles and lusters

Lifetime



LEDCandle CLA 4.3-40W E14 B35 Clear 827 ND



LEDCandle CLA 4.3-40W E14 B35 Clear 827 ND

