

FEATURES

- Flat probe tip
- Made of phosphor bronze
- Contact resistance of 30 mΩ
- Current rating of 3 A
- Length of 24.7 mm
- Pitch of 2.54 mm
- Spring pressure of 1.47 N(g)

RS PRO Flat Head, Test Probe, 3A

RS Stock No.: 261-5109



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Spring Test Probes



Product Description

If you regularly need to check the function of PCBs (printed circuit boards), stock up with this five-pack of spring test probes. They each come with a spring-loaded tip with a flat head, which provides a reliable electrical contact to a target at variable distances. Made of durable made of phosphor bronze, the probes are designed to operate without leaving marks or indentations.

General Specifications

Body Material	Phosphor bronze
Probe Tip Type	Flat Head
Body Plating	Gold
Durability	100000 Cycles
Applications	Test lands, pads, leads and holes Penetrates oxides and fluxes as well as contaminated boards

Electrical Specifications

Current Rating	3A
Contact Resistance	30mΩ

Mechanical Specifications

Pitch	2.54mm
Length	24.7mm
Full Travel	4.20mm

Operation Environment Specifications

Temperature Range	-40°C to 85°C
-------------------	---------------



Approvals

Compliance/Certifications EN61340



Dimensions (mm)

