

## HPP V4 Power insert crimp 250V/16A 3p



Image is for illustration purposes only. Please refer to product description.

Part number	09 46 500 3401
Specification	HPP V4 Power insert crimp 250V/16A 3p
HARTING eCatalogue	<a href="https://harting.com/09465003401">https://harting.com/09465003401</a>

### Identification

Category	Connectors
Series	HARTING PushPull (V4)
Identification	Power
Element	Female

### Version

Termination method	Crimp termination
Shielding	Unshielded
Number of contacts	2
PE contact	Yes
Locking type	PushPull
Pack contents	Without contacts

### Technical characteristics

Conductor cross-section	0.75 ... 2.5 mm <sup>2</sup> Stranded
Conductor cross-section [AWG]	AWG 20 ... AWG 12 Stranded
Wire outer diameter	≤2.9 mm
Rated current	16 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Stripping length	5 mm Cores 30 mm cable jacket



Pushing Performance  
Since 1945

## Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67

## Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

## Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

## Commercial data

Packaging size	100
Net weight	2.4 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140065536
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522