



Sample image

**Order symbol:** DH-3

**Product nbr:** 8524032

**Description:** DIN-35 Mounting rail, for enclosures:

**Remarks:** 170x80x65. 170x80x85. 170x140x95

**Including:**

**EAN:** 6418074033512

**El. number:**

- Finland: 3423916
- Denmark: 8212002270
- Sweden: 2536906

<b>Dimensions:</b>	<b>Height</b>	<b>Width</b>	<b>Depth</b>
mm:	140	35	1
inch:	5.51	1.38	0.04

**Materials:**

Material:

Base colour:

Cover colour:

Gasket material:

**Temperatures:**

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

**Rating:**

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C: C

NEMA Class

**Certificates:**