



### Main

Range	Acti9
Product or component type	Pan assembly
Device application	Distribution

### Complementary

[In] rated current	250 A
Incomer device	Switch disconnecter - 4P Terminal block - 4P RCCB - 3P + N MCCB - 3P + N Contactor - 4P
Protection device type	Miniature circuit breaker (MCB) 63 A max Residual current circuit breaker with overcurrent protection (RCBO) 45 A max Residual current circuit breaker with overcurrent protection (RCBO PoN) 45 A-max
Number of ways	24 ways - 3P + N + E
Short-circuit withstand	16 KA
Height	896 Mm
Width	375 Mm
Depth	105 Mm
Length	896 Mm
Busbar pitch	18 Mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.700 Cm
Package 1 Width	41.100 Cm
Package 1 Length	92.600 Cm
Package 1 Weight	10.362 Kg
Unit Type of Package 2	PAM
Number of Units in Package 2	16
Package 2 Height	110.000 Cm
Package 2 Width	100.000 Cm
Package 2 Length	120.000 Cm
Package 2 Weight	185.792 Kg

### Environmental data

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product
Take-back	No

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : <b>Commercialised</b>
---