

## FEATURES

- 5 mm high contrast coloured diffused epoxy lens
- Rated at IP67
- Solder tab terminals
- Gold terminals (Anode +ve)
- Various voltage ratings

## RS PRO Green Indicator, 24 V ac/dc, 8mm Mounting Hole Size, Solder Tab Termination, IP67

RS Stock No.: 204-962



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

Brought to you by RS Pro, a range of LED indicators. Each indicator has a compact and robust high quality build, complete with a solder tab termination. The relative ease of the installation process ensures these LED indicators are perfect for your application. With tri-colour options available, the possibilities are endless. Whether the intended application is a signal, warning or purely a display, there are choices to suit all outcomes. All models are highly reliable and excellent quality.

### General Specifications

<b>Light Output Colour</b>	Green
<b>Lamp Type</b>	LED
<b>Termination Type</b>	Solder Tab
<b>Type</b>	Panel Mount
<b>Bezel Style</b>	Recessed
<b>Bezel Colour</b>	Chrome
<b>Intensity</b>	40mcd
<b>Type Of Illumination</b>	Fixed Light
<b>LED Colour</b>	Tricolour
<b>Viewing Angle</b>	30° to 100°
<b>Life Expectancy</b>	100000hours
<b>Applications</b>	Fixed to PCB circuit boards mounted; Switches; Pushbuttons; Used as vehicle indicators

### Electrical Specifications

<b>Voltage Rating</b>	24V ac/dc
<b>Current Rating</b>	20mA
<b>Voltage Tolerance</b>	10%

**Mechanical Specifications**

Mounting Hole Size	8mm
Length	41mm
Lamp Size	5mm

**Operation Environment Specifications**

Temperature Rating	-40°C to 85°C
--------------------	---------------

**Protection Category**

IP Rating	IP67
-----------	------

**Approvals**

Compliance/Certifications	EN61340
---------------------------	---------

