



SDS-Plus M2 10 x 210 - 1 pc

SDS-PLUS M2 DRILL BITS - 2 CUT

- Breaker Points. 3 offset aggressive power breakers. These produce a "Demolition" effect and create micro cracks in the drilled material. Up to 25% FASTER
- Centering tip. Ensures immediate spot drilling with pin point accuracy. Prevents skidding on smooth surfaces
- Enlarged rebar chamfers. Prevents side tip damage when hitting rebar. Reduces the risk of the drill bit jamming when hitting rebar
- Tapered shoulder design. Thinner shoulder towards drill tip for less friction providing for greater speed. Ideal for cordless hammers identified from its tapered shoulder geometry
- Reinforced flute. High volume flute geometry for optimum dust removal. Reinforced flute design (thicker core) gives: - Full power transfer to the tip. - Lower vibrations. - Exceptional break resistance, less breakages and best durability
- Made in Germany
- FASTEST: New aggressive tip geometry with 3 chip breakers demolishes the concrete quicker and a tapered shoulder design minimises friction enabling the M2 drill bit to deliver faster drilling speed
- DURABILITY: Rebar chamfers on the tip prevent side tip damage when hitting metal reinforcement and a thicker core body ensures higher power transfer, lower vibrations and less flute breakages



ø (mm)	10
Article Number	4932307074
Pack quantity	1
Quantity	1
Total length (mm)	210
Working length (mm)	150