

Product Data Sheet

MaxiFlex® Active™ 34-824

Colour – Coating	Light blue
Colour – Liner	Light blue
Design	Palm coated knitwrist
Coating	NBR (Nitrile Butadiene Rubber)
Coating texture	Micro-Foam for Controlled Grip
Liner	Nylon, Spandex
Patent number	EP 1 608 808
Palm thickness	1.00 mm



Dimensions

Size Range	Size 5 (XXS)	Size 6 (XS)	Size 7 (S)	Size 8 (M)	Size 9 (L)	Size 10 (XL)	Size 11 (XXL)
Total glove length (+/-10 mm)	185	195	205	215	225	230	235
Wrist length (mm)	55	60	65	65	70	70	70
Wrist width (mm)	65	65	65	70	75	75	80
Palm width (+/-3 mm)	75	81	83	89	95	97	100
Over lock colour	Purple	Blue	Red	Orange	White	Yellow	Black

EN test Results

Test	Notified Body	Result/Pass
EN ISO 21420: 2020	TÜV Rheinland	Yes
EN 388: 2016 + A1: 2018	TÜV Rheinland	4131A



Product Data Sheet

MaxiFlex® Active™ 34-824

Typical Performance Values

EN ISO 21420 Dexterity	Level 5
EN 388:2016 + A1:2018 A. Abrasion Resistance	> 8000 Cycles
EN 388:2016 + A1:2018 B. Cut Resistance	> 1.2 index
EN 388:2016 + A1:2018 C. Tear Resistance	> 50 newtons
EN 388:2016 + A1:2018 D. Puncture Resistance	> 20 newtons
EN 388:2016 + A1:2018 E. Cut Resistance ISO	≥ 2 Newton

HandCare®

Skin Health Alliance Dermatologically Accredited	Yes
REACH compliant	Yes
Standard 100 by OEKO-TEX® (08.BH.57867)	Certified
Washable	40°
Sanitized®	Yes



Special features

Silicone free	Yes
---------------	-----

Packaging

Pairs per poly bag	12
Poly bags per carton	12
Carton count	144
Carton dimensions (mm)	500 x 295 x 270



Product Data Sheet

MaxiFlex® Active™ 34-824

Weight

Size Range	Size 5 (XXS)	Size 6 (XS)	Size 7 (S)	Size 8 (M)	Size 9 (L)	Size 10 (XL)	Size 11 (XXL)
Glove weight / Pair (+/- 6 gram)	26	28	32	38	40	42	44
Gross Weight (Kg)	5	5.3	5.9	6.7	7	7.3	7.6
Carton Weight (Kg)	1	1	1	1	1	1	1
Net Weight (Kg)	4	4.3	4.9	5.7	6	6.3	6.6

Issue date: 18.07.2019

