

## FEATURES

- Flexible coolant hose starter kit
- Used for 1/4 in modular hose systems
- One 11 in hose
- Three nozzles with sizes of 1/16 in, 1/8 in and 1/4 in
- Two NPT connectors with sizes of 1/8 in and 1/4 in
- Made from heat-resistant polyoxymethylene
- Maximum liquid pressure of 0.19 Pa
- Maximum air pressure of 0.35 Pa
- Hose is blue in colour (Pantone 3025C)
- Hose internal diameter of 6.7 mm
- Hose external diameter of 16.3 mm

## RS PRO 1/4in Hose Kit

RS Stock No.: 623-5397



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

This flexible coolant hose starter kit contains the accessories you need to build an initial coolant hose system for preventing machines from overheating. The kit comes with one 11 in hose that accommodates a maximum flow of 16 m<sup>3</sup>/h and a maximum pressure of 0.19 Pa for liquid or 0.34 Pa for air. You also get three nozzles (1/16 in, 1/8 in and 1/4 in) and two national pipe thread (NPT) connectors (1/8 in and 1/4 in). As part of the RS PRO series, this kit is tested for quality and safety. The components have a polyoxymethylene construction for extra durability and resistance to heat.

### General Specifications

Type	Starter Kit
Systems	1/4in
Material	Acetal Copolymer
Kit Contents	1/4 in Nozzle, 1/4 in NPT connector, 1/8 in Nozzle, 1/8 in NPT connector, 1/16 in Nozzle, 11 in Hose

### Mechanical Specifications

Size	1/4in
Internal Diameter	6.7mm
External Diameter	16.3mm

### Operation Environment Specifications

Maximum Pressure Liquid/Air	0.19/0.35Pa
-----------------------------	-------------

### Approvals

Compliance/Certifications	EN61340
---------------------------	---------



