

Rexel Optimum AutoFeed+ 750X Automatic Cross Cut Paper Shredder

The Optimum AutoFeed+ 750X cross cut shredder automatically shreds up to 750x A4 sheets of paper (80gsm) at a time, into P-4 (4x30mm) cross cut pieces. This auto feed shredder machine is a sophisticated office shredder, featuring a 140L pull out bin. No need to manually feed paper, or remove staples and paper clips first, this automatic paper shredder will do all the work for you.



Attributes

- Auto feed up to 750 sheets of A4 paper (80gsm) at a time. Manual slot for up to 20 sheets.
- P-4 cross cut (4x30mm)
- 140L high capacity cabinet bin. Plastic shredder bag dispenser inside the bin door for convenient bag replacement.
- Castor wheels for ease of movement around the workplace.
- Anti-jam technology
- Shreds credit cards, staples and paper clips.
- 240 minutes continuous run time with fan cooling. Sleep mode activates after 3 minutes of non use.
- Touch control panel with pin code lock for ultimate confidence and security.
- 55 dBA ultra-quiet noise level
- Infra red bin full sensor
- 2 year warranty, 2 year cutter warranty



Specifications

Number	2020750X
Colour	black
Dimensions (W x H x D)	510 x 1133 x 570 mm
Cut Type	Cross Cut
Maximum Slot Entry Width (mm)	230
Run Time From Cold (min)	240
Shredded Particle Width mm	4x30
Security Level	P-4
Cutting Capacity sheets (70gsm paper)	825
Cutting Capacity sheets (80gsm paper)	750
Container/collection volume in l	140
Shreds	Paper, Credit cards, Paper clips & Staples
Power consumption (W)	700
Noise Level (dBA)	55
Period of Warranty (Years)	2
Location	Large Office
Number Of Users	10+
Weight	52000 g
Pallet quantity	1
EAN code	5028252606332