







- ① .000030 THICK GOLD OVER NICKEL ON INSIDE OF RECEPTACLE; REMAINDER OF CONTACT IS NICKEL PLATED.
- ② .000030 THICK GOLD OVER NICKEL ON INSIDE OF RECEPTACLE AND WIRE BARREL; REMAINDER OF CONTACT IS NICKEL PLATED.

350689-7	GOLD	.010 BRASS	350570-7
—		.010 PH. BRZ	350570-6
350689-3	PRE-TIN	.00 PH. BRZ	350570-3
350689-2	GOLD	.010 BRASS	350570-2
350689-1	PRE-TIN		350570-1
LOOSE PIECE (REF)	FINISH	MATERIAL	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.010 ANGLES ±	CONTRACT NO	TE TE Connectivity		
	DR M. FEHER 5-26-81			
	CHK J.S. Heide 6/9/81	NAME	SOCKET, UNIVERSAL MATE-N-LOK	
	WIRE RANGE 24-18 AWG	APPD R. P. B. 6-10-81	SIZE	FSCM NO
INSULATION RANGE .100 DIA MAX	DSGN APPD	B	00779	350570
	OTHER APPD	SCALE 4-1	SHEET 1-1	