



ENGLISH

# Datasheet

## Scissors

# 6" clamp/locking scissors



[RS Stock No. 444-4088](#)

**Material:** Drop forged stainless steel (#sus-420j2) for clamp/scissors.

**Finish:** Matt finish for pliers.

**Hardness:** Heat treated to hrc: 38-45 degree.

**Contents:**

6in clamp/scissors with 3-positions, ratchet action lock, straight jaw & box joint construction (firmly gripping to copper wire up to 0.10mm).

Overall length: 155.0mm

Jaw length: 33.0mm

Serrated length: 30.0mm

Nose width: 2.5mm

Nose thickness: 2.30mm

Handle spin: 70.0mm