



Datasheet

RS PRO Worm Drive Zinc Plated Mild Steel Hose Clips Kit

Stock number: 175-7152

EN



Stock no	Description	Range		Quantity
		mm	in	Pieces
1450243	Worm drive Mild Steel, 9.5 mm band w, 9.5-12 D (OOO)	9.5 – 12	3/8 - 1/2	10
1450244	Worm drive Mild Steel, 9.5 mm band w, 11-16 D (MOO)	11 – 16	1/2 - 5/8	10
1450245	Worm drive Mild Steel, 9.5 mm band w, 13-20 D (OO)	13 – 20	1/2 - 3/4	20
1450246	Worm drive Mild Steel, 12.0 mm band w, 16-22 D (O)	16 – 22	5/8 - 7/8	8
1450247	Worm drive Mild Steel, 12.0mm band w, 18-25 D (OX)	18 – 25	3/4 - 1	8
1450248	Worm drive Mild Steel, 12.0 mm band w, 22-30 D (1A)	22 – 30	7/8 - 1 1/8	8
1450249	Worm drive Mild Steel, 12.0 mm band w, 25-35 D (1)	25 – 35	1 - 1 3/8	5
	Screwdriver			1